


BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	RECOMMENDED TOOLING
YF2406IWL	TURQUOISE	24	0.34	.39 [10.0]	.24 [6.0]	.04 [1.1]	.03 [0.80]	.08 [1.9]	YF268CFSL YF261CSKIT WITH YF2610D DIE
YF2408IWL				.47 [12.0]	.32 [8.0]	.04 [1.1]	.03 [0.80]	.08 [1.9]	
YF2206IWL	ORANGE	22	0.5	.47 [12.0]	.24 [6.0]	.05 [1.3]	.04 [1.0]	.10 [2.6]	
YF2208IWL				.55 [14.0]	.32 [8.0]	.05 [1.3]	.04 [1.0]	.10 [2.6]	
YF2210IWL				.63 [16.0]	.39 [10.0]	.05 [1.3]	.04 [1.0]	.10 [2.6]	
YF2212IWL				.71 [18.0]	.47 [12.0]	.05 [1.3]	.04 [1.0]	.10 [2.6]	
YF2006IWL	WHITE	20	0.75	.47 [12.0]	.24 [6.0]	.06 [1.5]	.05 [1.2]	.11 [2.8]	
YF2008IWL				.55 [14.0]	.32 [8.0]	.06 [1.5]	.05 [1.2]	.11 [2.8]	
YF2010IWL				.63 [16.0]	.39 [10.0]	.06 [1.5]	.05 [1.2]	.11 [2.8]	
YF2012IWL				.71 [18.0]	.47 [12.0]	.06 [1.5]	.05 [1.2]	.11 [2.8]	
YF1806IWL	YELLOW	18	1	.47 [12.0]	.24 [6.0]	.07 [1.7]	.06 [1.4]	.12 [3.0]	
YF1808IWL				.55 [14.0]	.32 [8.0]	.07 [1.7]	.06 [1.4]	.12 [3.0]	
YF1810IWL				.63 [16.0]	.39 [10.0]	.07 [1.7]	.06 [1.4]	.12 [3.0]	
YF1812IWL				.71 [18.0]	.47 [12.0]	.07 [1.7]	.06 [1.4]	.12 [3.0]	
YF1818IWL				.94 [24.0]	.71 [18.0]	.07 [1.7]	.06 [1.4]	.12 [3.0]	

BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	RECOMMENDED TOOLING
YF1606IWL *	RED	16	1.5	.47 [12.0]	.24 [6.0]	0.08 [2.0]	.07 [1.7]	.14 [3.5]	YF268CFSL YF261CSKIT WITH YF2610D DIE
YF1608IWL				.55 [14.0]	.32 [8.0]	0.08 [2.0]	.07 [1.7]	.14 [3.5]	
YF1610IWL				.63 [16.0]	.39 [10.0]	0.08 [2.0]	.07 [1.7]	.14 [3.5]	
YF1612IWL				.71 [18.0]	.47 [12.0]	0.08 [2.0]	.07 [1.7]	.14 [3.5]	
YF1618IWL	BLUE	14	2.5	.94 [24.0]	.71 [18.0]	0.08 [2.0]	.07 [1.7]	.14 [3.5]	
YF1408IWL				.55 [14.0]	.32 [8.0]	0.10 [2.5]	.09 [2.2]	.17 [4.2]	
YF1410IWL				.63 [16.0]	.39 [10.0]	0.10 [2.5]	.09 [2.2]	.17 [4.2]	
YF1412IWL				.71 [18.0]	.47 [12.0]	0.10 [2.5]	.09 [2.2]	.17 [4.2]	
YF1418IWL				.94 [24.0]	.71 [18.0]	0.10 [2.5]	.09 [2.2]	.17 [4.2]	
YF1209IWL *	GRAY	12	4	.67 [17.0]	.35 [9.0]	0.13 [3.2]	.11 [2.8]	.19 [4.8]	
YF1210IWL				.67 [17.0]	.39 [10.0]	0.13 [3.2]	.11 [2.8]	.19 [4.8]	
YF1212IWL				.79 [20.0]	.47 [12.0]	0.13 [3.2]	.11 [2.8]	.19 [4.8]	
YF1218IWL				1.02 [26.0]	.71 [18.0]	0.13 [3.2]	.11 [2.8]	.19 [4.8]	

NOTES:

1. MATERIAL: COPPER.
2. FINISH : TIN PLATED
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
4. UL LISTED BARE AND COVERED FERRULES PER UL486F REQUIREMENTS.
5. ITEMS WITH CATALOG NUMBERS FOLLOWED BY ASTERISKS (*) ARE NOT UL LISTED.



TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-387-6487

FOR PRODUCT INFO: <http://www.burndy.com>

INSULATED FERRULES

ITEM NO: SEE TABLE

CAT. NO: SEE TABLE

DRAWN BY: M.SAURABH12/07/2020

CHECKER: K.HERNANDEZ10/18/2022

DSN APRVL: K.HERNANDEZ10/18/2022

MFG APRVL: --

QA APRVL: J.BRODEUR05/10/2021

MKT APRVL: A.FITZGER05/12/2021

PROJ FAM: --

PROJECT #: --

DOCUMENT TYPE: SALES

REL LEVEL: Released

SIZE

D

DRAWING NO

50111876

SHEET 1 OF 6

REV

A



BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	RECOMMENDED TOOLING
YF1010IWL*	BLACK	10	6	.71 [18.0]	.39 [10.0]	0.15 [3.9]	.14 [3.5]	.25 [6.3]	YF268CFSL
YF1012IWL				.79 [20.0]	.47 [12.0]		.14 [3.5]	.25 [6.3]	YF261CSKIT WITH YF2610D DIE
YF1018IWL				1.02 [26.0]	.71 [18.0]		.14 [3.5]	.25 [6.3]	
YF0812IWL	IVORY	8	10	.87 [22.0]	.47 [12.0]	0.19 [4.9]	.18 [4.5]	.30 [7.6]	YF268CFSL
YF0818IWL				1.10 [28.0]	.71 [18.0]				YF261CSKIT WITH YF864D DIE
YF0612IWL	GREEN	6	16	.94 [24.0]	.47 [12.0]	0.24 [6.2]	.23 [5.8]	.35 [8.8]	YF261CSKIT WITH YF864D DIE
YF0618IWL				1.10 [28.0]	.71 [18.0]		.23 [5.8]	.35 [8.8]	
YF0412IWL*	BROWN	4	25	1.02 [26.0]	.47 [12.0]	0.30 [7.7]	.29 [7.3]	.44 [11.2]	
YF0415IWL*				1.14 [29.0]	.59 [15.0]		.29 [7.3]	.44 [11.2]	
YF0416IWL				1.18 [30.0]	.63 [16.0]		.29 [7.3]	.44 [11.2]	
YF0218IWL	BEIGE	2	35	1.26 [32.0]	.71 [18.0]	0.34 [8.7]	.33 [8.3]	.50 [12.7]	
YF2205IDL*	WHITE	22	0.5	.43 [11.0]	.20 [5.0]	0.05 [1.3]	.04 [1.0]	.10 [2.6]	YF268CFSL
YF2206IDL				.47 [12.0]	.24 [6.0]		.04 [1.0]	.10 [2.6]	YF261CSKIT WITH YF2610D DIE

BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	RECOMMENDED TOOLING
YF2208IDL	WHITE	22	0.5	.55 [14.0]	.31 [8.0]	0.05 [1.3]	.04 [1.0]	.10 [2.6]	YF268CFSL YF261CSKIT WITH YF2610D DIE
YF2210IDL				.63 [16.0]	.40 [10.0]		.04 [1.0]	.10 [2.6]	
YF2212IDL				.71 [18.0]	.47 [12.0]		.04 [1.0]	.10 [2.6]	
YF2006IDL	GRAY	20	0.75	.47 [12.0]	.24 [6.0]	0.06 [1.5]	.05 [1.2]	.11 [2.8]	
YF2008IDL				.55 [14.0]	.31 [8.0]		.05 [1.2]	.11 [2.8]	
YF2010IDL				.63 [16.0]	.40 [10.0]		.05 [1.2]	.11 [2.8]	
YF2012IDL	RED	18	1	.71 [18.0]	.47 [12.0]	0.07 [1.7]	.05 [1.2]	.11 [2.8]	
YF2018IDL				.94 [24.0]	.71 [18.0]		.05 [1.2]	.11 [2.8]	
YF1806IDL				.47 [12.0]	.24 [6.0]		.06 [1.4]	.12 [3.0]	
YF1808IDL	RED	18	1	.55 [14.0]	.31 [8.0]	0.07 [1.7]	.06 [1.4]	.12 [3.0]	
YF1810IDL				.63 [16.0]	.40 [10.0]		.06 [1.4]	.12 [3.0]	
YF1812IDL				.71 [18.0]	.47 [12.0]		.06 [1.4]	.12 [3.0]	
YF1818IDL				.94 [24.0]	.71 [18.0]		.06 [1.4]	.12 [3.0]	

NOTES:

1. MATERIAL: COPPER.
2. FINISH : TIN PLATED
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
4. UL LISTED BARE AND COVERED FERRULES PER UL486F REQUIREMENTS.
5. ITEMS WITH CATALOG NUMBERS FOLLOWED BY ASTERISKS (*) ARE NOT UL LISTED.

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-387-6487

FOR PRODUCT INFO: <http://www.burndy.com>

INSULATED FERRULES

ITEM NO: SEE TABLE

CAT. NO: SEE TABLE

DRAWN BY: M.SAURABH12/07/2020

CHECKER: K.HERNANDEZ10/18/2022

DSN APRVL: K.HERNANDEZ10/18/2022

MFG APRVL: --

QA APRVL: J.BRODEUR05/10/2021

MKT APRVL: A.FITZGER05/12/2021

PROD FAM: --

PROJECT #: --

DOCUMENT TYPE: SALES

REL LEVEL: Released

SIZE

D

DRAWING NO

50111876

SHEET 2 OF 6

REV

A




BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	RECOMMENDED TOOLING	BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	RECOMMENDED TOOLING
YF1606IDL*	BLACK	16	1.5	.47 [12.0]	.24 [6.0]	.08 [2.0]	.07 [1.7]	.14 [3.5]	YF268CFSL YF261CSKIT WITH YF2610D DIE	YF1010IDL*	YELLOW	10	6	.71 [18.0]	.39 [10.0]	.15 [3.9]	.14 [3.5]	.25 [6.3]	YF268CFSL YF261CSKIT WITH YF2610D DIE
YF1608IDL				.55 [14.0]	.31 [8.0]		.07 [1.7]	.14 [3.5]		YF1012IDL				.79 [20.0]	.47 [12.0]		.14 [3.5]	.25 [6.3]	
YF1610IDL				.63 [16.0]	.40 [10.0]		.07 [1.7]	.14 [3.5]		YF1018IDL				1.02 [26.0]	.71 [18.0]		.14 [3.5]	.25 [6.3]	
YF1612IDL				.71 [18.0]	.47 [12.0]		.07 [1.7]	.14 [3.5]		YF0812IDL	RED	8	10	.87 [22.0]	.47 [12.0]	.19 [4.9]	.18 [4.5]	.30 [7.6]	YF268CFSL YF261CSKIT WITH YF864D DIE
YF1615IDL				.83 [21.0]	.59 [15.0]		.07 [1.7]	.14 [3.5]		YF0815IDL				.98 [25.0]	.59 [15.0]		.18 [4.5]	.30 [7.6]	
YF1618IDL				.94 [24.0]	.71 [18.0]		.07 [1.7]	.14 [3.5]		YF0818IDL				1.10 [28.0]	.71 [18.0]		.18 [4.5]	.30 [7.6]	
YF1408IDL	BLUE	14	2.5	.55 [14.0]	.31 [8.0]	.10 [2.5]	.09 [2.2]	.17 [4.2]		YF0612IDL	BLUE	6	16	.94 [24.0]	.47 [12.0]	.24 [6.2]	.23 [5.8]	.35 [8.8]	YF261CSKIT WITH YF864D DIE
YF1410IDL				.63 [16.0]	.40 [10.0]		.09 [2.2]	.17 [4.2]		YF0618IDL				1.10 [28.0]	.71 [18.0]		.23 [5.8]	.35 [8.8]	
YF1412IDL				.71 [18.0]	.47 [12.0]		.09 [2.2]	.17 [4.2]		YF0412IDL*	YELLOW	4	25	1.02 [26.0]	.47 [12.0]	.30 [7.7]	.29 [7.3]	.44 [11.2]	
YF1418IDL				.94 [24.0]	.71 [18.0]		.09 [2.2]	.17 [4.2]		YF0415IDL*				1.14 [29.0]	.59 [15.0]		.29 [7.3]	.44 [11.2]	
YF1209IDL*	GRAY	12	4	.67 [17.0]	.35 [9.0]	.13 [3.2]	.11 [2.8]	.19 [4.8]		YF0416IDL				1.18 [30.0]	.63 [16.0]		.29 [7.3]	.44 [11.2]	
YF1210IDL				.67 [17.0]	.39 [10.0]		.11 [2.8]	.19 [4.8]		YF0418IDL				1.26 [32.0]	.71 [18.0]		.29 [7.3]	.44 [11.2]	
YF1212IDL				.79 [20.0]	.47 [12.0]		.11 [2.8]	.19 [4.8]		YF0422IDL				1.42 [36.0]	.87 [22.0]		.29 [7.3]	.44 [11.2]	
YF1218IDL				1.02 [26.0]	.71 [18.0]		.11 [2.8]	.19 [4.8]		YF0425IDL				1.54 [39.0]	.98 [25.0]		.29 [7.3]	.44 [11.2]	

NOTES:

1. MATERIAL: COPPER.
2. FINISH : TIN PLATED
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
4. UL LISTED BARE AND COVERED FERRULES PER UL486F REQUIREMENTS.
5. ITEMS WITH CATALOG NUMBERS FOLLOWED BY ASTERISKS (*) ARE NOT UL LISTED.

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-387-6487

FOR PRODUCT INFO: <http://www.burndy.com>

INSULATED FERRULES

ITEM NO: SEE TABLE

CAT. NO: SEE TABLE

DRAWN BY: M.SAURABH12/07/2020

CHECKER: K.HERNANDEZ10/18/2022

DSN APRVL: K.HERNANDEZ10/18/2022

MFG APRVL: --

QA APRVL: J.BRODEUR05/10/2021

MKT APRVL: A.FITZGER05/12/2021

PROD FAM: --

PROJECT #: --

DOCUMENT TYPE: SALES

REL LEVEL: Released

SIZE

D

DRAWING NO

50111876

SHEET 3 OF 6

REV

A


BURNDY

BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	RECOMMENDED TOOLING	BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	RECOMMENDED TOOLING
YF0216IDL	RED	2	35	1.18 [30.0]	.63 [16.0]	.34 [8.7]	.32 [8.3]	0.50 [12.7]	YF261CSKIT WITH YF21D DIE	YF2/020IDL*	YELLOW	2/0	70	1.46 [37.0]	.83 [21.0]	.56 [14.3]	.53 [13.5]	.63 [16.0]	--
YF0218IDL				1.26 [32.0]	.71 [18.0]		.32 [8.3]	0.50 [12.7]		YF2/025IDL*				1.61 [41.0]	.98 [25.0]		.53 [13.5]	.63 [16.0]	
YF0222IDL				1.42 [36.0]	.87 [22.0]		.32 [8.3]	0.50 [12.7]		YF2/032IDL*				1.73 [44.0]	28.0		.53 [13.5]	.63 [16.0]	
YF0225IDL				1.54 [39.0]	.98 [25.0]		.32 [8.3]	0.50 [12.7]		YF3/025IDL*	RED	3/0	95	1.73 [44.0]	.98 [25.0]	.61 [15.5]	.58 [14.7]	.71 [18.0]	
YF0112IDL*	BLUE	1	50	1.10 [28.0]	.47 [12.0]	.43 [10.9]	.41 [10.3]	.59 [15.0]	81KFT SERIES YF261CSKIT WITH YF21D DIE	YF2406ITL	PINK	24	0.34	.39 [10.0]	.24 [6.0]	.04 [1.1]	.03 [0.80]	.08 [1.9]	YF268CFSL YF261CSKIT WITH YF2610D DIE
YF0116IDL*				1.26 [32.0]	.63 [16.0]		.41 [10.3]	.59 [15.0]		YF2408ITL				.47 [12.0]	.32 [8.0]		.03 [0.80]	.08 [1.9]	
YF0120IDL*				1.42 [36.0]	.79 [20.0]		.41 [10.3]	.59 [15.0]		YF2206ITL	WHITE	22	0.5	.47 [12.0]	.24 [6.0]	.05 [1.3]	.04 [1.0]	.10 [2.6]	
YF0122IDL*				1.46 [37.0]	.83 [21.0]		.41 [10.3]	.59 [15.0]		YF2208ITL				.55 [14.0]	.32 [8.0]		.04 [1.0]	.10 [2.6]	
YF0125IDL*				1.57 [40]	.98 [25.0]		.41 [10.3]	.59 [15.0]		YF2210ITL				.63 [16.0]	.39 [10.0]		.04 [1.0]	.10 [2.6]	
YF1/012IDL*		1/0	50	1.10 [28.0]	.47 [12.0]		.41 [10.3]	.59 [15.0]		YF2212ITL				.71 [18.0]	.47 [12.0]		.04 [1.0]	.10 [2.6]	
YF1/016IDL*				1.26 [32.0]	.63 [16.0]		.41 [10.3]	.59 [15.0]		YF2006ITL	BLUE	20	0.75	.47 [12.0]	.24 [6.0]	0.06 [1.5]	.05 [1.2]	.11 [2.8]	
YF1/020IDL				1.42 [36.0]	.79 [20.0]		.41 [10.3]	.59 [15.0]		YF2008ITL				.55 [14.0]	.32 [8.0]		.05 [1.2]	.11 [2.8]	
YF1/022IDL				1.46 [37.0]	.83 [21.0]		.41 [10.3]	.59 [15.0]		YF2010ITL				.63 [16.0]	.39 [10.0]		.05 [1.2]	.11 [2.8]	
YF1/025IDL				1.57 [40.0]	.98 [25.0]		.41 [10.3]	.59 [15.0]		YF2012ITL				.71 [18.0]	.47 [12.0]		.05 [1.2]	.11 [2.8]	

NOTES:

1. MATERIAL: COPPER.
2. FINISH : TIN PLATED
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
4. UL LISTED BARE AND COVERED FERRULES PER UL486F REQUIREMENTS.
5. ITEMS WITH CATALOG NUMBERS FOLLOWED BY ASTERISKS (*) ARE NOT UL LISTED.

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-387-6487

FOR PRODUCT INFO: <http://www.burndy.com>

INSULATED FERRULES

ITEM NO: SEE TABLE

CAT. NO: SEE TABLE

DRAWN BY: M.SAURABH12/07/2020

CHECKER: K.HERNANDEZ10/18/2022

DSN APRVL: K.HERNANDEZ10/18/2022

MFG APRVL: --

QA APRVL: J.BRODEUR05/10/2021

MKT APRVL: A.FITZGER05/12/2021

PROJ FAM: --

PROJECT #: --

DOCUMENT TYPE: SALES

REL LEVEL: Released





DRAWING NO

50111876

SHEET 4 OF 6

REV

A

REV	DATE	DESCRIPTION	EC	BY	C'H'K.
A	04/05/2021	NEW DRAWING CREATION	210405006822	SS	YR

BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	RECOMMENDED TOOLING
YF1806ITL	RED	18	1	.47 [12.0]	.24 [6.0]	.07 [1.7]	.06 [1.4]	3.0 [.12]	YF268CFSL YF261CSKIT WITH YF2610D DIE
YF1808ITL				.55 [14.0]	.32 [8.0]		.06 [1.4]	3.0 [.12]	
YF1810ITL				.63 [16.0]	.39 [10.0]		.06 [1.4]	3.0 [.12]	
YF1812ITL				.71 [18.0]	.47 [12.0]		.06 [1.4]	3.0 [.12]	
YF1818ITL				.94 [24.0]	.71 [18.0]		.06 [1.4]	3.0 [.12]	
YF1606ITL*	BLACK	16	1.5	.47 [12.0]	.24 [6.0]	.08 [2.0]	.07 [1.7]	.14 [3.5]	
YF1608ITL				.55 [14.0]	.32 [8.0]		.07 [1.7]	.14 [3.5]	
YF1610ITL				.63 [16.0]	.39 [10.0]		.07 [1.7]	.14 [3.5]	
YF1612ITL				.71 [18.0]	.47 [12.0]		.07 [1.7]	.14 [3.5]	
YF1618ITL				.94 [24.0]	.71 [18.0]		.07 [1.7]	.14 [3.5]	
YF1408ITL	GRAY	14	2.5	.55 [14.0]	.32 [8.0]	.10 [2.6]	.09 [2.2]	.17 [4.2]	
YF1410ITL				.63 [16.0]	.39 [10.0]		.09 [2.2]	.17 [4.2]	
YF1412ITL				.71 [18.0]	.47 [12.0]		.09 [2.2]	.17 [4.2]	
YF1418ITL				.94 [24.0]	.71 [18.0]		.09 [2.2]	.17 [4.2]	

BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	RECOMMENDED TOOLING
YF1209ITL*	ORANGE	12	4	.67 [17.0]	.35 [9.0]	.13 [3.2]	.11 [2.8]	.19 [4.8]	YF268CFSL YF261CSKIT WITH YF2610D DIE
YF1210ITL				.67 [17.0]	.39 [10.0]		.11 [2.8]	.19 [4.8]	
YF1212ITL				.79 [20.0]	.47 [12.0]		.11 [2.8]	.19 [4.8]	
YF1218ITL				1.02 [26.0]	.71 [18.0]		.11 [2.8]	.19 [4.8]	
YF1010ITL*	GREEN	10	6	.71 [18.0]	.39 [10.0]	.15 [3.9]	.14 [3.5]	.24 [6.3]	
YF1012ITL				.79 [20.0]	.47 [12.0]		.14 [3.5]	.24 [6.3]	
YF1018ITL				1.02 [26.0]	.71 [18.0]		.14 [3.5]	.24 [6.3]	
YF0812ITL	BROWN	8	10	.87 [22.0]	.47 [12.0]	.19 [4.9]	.18 [4.5]	.30 [7.6]	YF268CFSL YF261CSKIT WITH YF864D DIE
YF0818ITL				1.10 [28.0]	.71 [18.0]		.18 [4.5]	.30 [7.6]	
YF0612ITL	IVORY	6	16	.94 [24.0]	.47 [12.0]	.24 [6.2]	.23 [5.8]	.35 [8.8]	YF261CSKIT WITH YF864D DIE
YF0618ITL				1.10 [28.0]	.71 [18.0]		.23 [5.8]	.35 [8.8]	
YF0416ITL	BLACK	4	25	1.18 [30.0]	.63 [16.0]	.30 [7.7]	.29 [7.3]	.44 [11.2]	
YF0218ITL	RED	2	35	1.26 [32.0]	.71 [18.0]	.34 [8.7]	.33 [8.3]	.5 [12.7]	YF261CSKIT WITH YF21D DIE


NOTES:

1. MATERIAL: COPPER.
2. FINISH : TIN PLATED
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
4. UL LISTED BARE AND COVERED FERRULES PER UL486F REQUIREMENTS.
5. ITEMS WITH CATALOG NUMBERS FOLLOWED BY ASTERISKS (*) ARE NOT UL LISTED.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-387-6487 FOR PRODUCT INFO: http://www.burndy.com	INSULATED FERRULES				
	ITEM NO: SEE TABLE				
	CAT. NO: SEE TABLE				
	DRAWN BY: M.SAURABH		12/07/2020		 
	CHECKER: K.HERNANDEZ		10/18/2022		
	DSN APRVL: K.HERNANDEZ		10/18/2022		
	MFG APRVL: --				
	QA APRVL: J.BRODEUR		05/10/2021		
	MKT APRVL: A.FITZGER		05/12/2021		
	PROD FAM: --				DRAWING NO
PROJECT #: --		SIZE		50111876	A
DOCUMENT TYPE: SALES		D			
REL LEVEL: Released					
				SHEET 5 OF 6	

BURNDY CAT NO.	COLOR CODE	AWG	mm ²	L1	L2	D	D1	D2	E	RECOMMENDED TOOLING
YFTW2208DL	WHITE	22	0.5	.59 [15.0]	.32 [8.0]	.07 [1.8]	.06 [1.5]	.19 [4.7]	.10 [2.5]	YF268CFSL YF261CSKIT WITH YF2610D DIE
YFTW2008DL	GRAY	20	0.8	.59 [15.0]	.32 [8.0]	.08 [2.1]	.07 [1.8]	.20 [5.0]	.11 [2.8]	
YFTW2010DL				.67 [17.0]	.39 [10.0]		.07 [1.8]	.20 [5.0]	.11 [2.8]	
YFTW1808DL	RED	18	1	.59 [15.0]	.32 [8.0]	.09 [2.4]	.08 [2.05]	.21 [5.4]	.13 [3.4]	
YFTW1810DL				.67 [17.0]	.39 [10.0]		.08 [2.05]	.21 [5.4]	.13 [3.4]	
YFTW1608DL	BLACK	16	1.5	.63 [16.0]	.32 [8.0]	0.10 [2.6]	.09 [2.2]	.26 [6.6]	.14 [3.6]	
YFTW1612DL				.79 [20.0]	.47 [12.0]		.09 [2.2]	.26 [6.6]	.14 [3.6]	
YFTW1410DL	BLUE	14	2.5	.73 [18.5]	.39 [10.0]	.127 [3.2]	.11 [2.8]	.31 [7.8]	.17 [4.2]	
YFTW1413DL	BLUE			.85 [21.5]	.51 [13.0]	0.13 [3.3]	.11 [2.8]	.31 [7.8]	.17 [4.2]	
YFTW1212DL	GRAY	12	4	.91 [23.0]	.47 [12.0]	.17 [4.2]	.15 [3.7]	.35 [8.8]	.19 [4.9]	
YFTW1014DL	YELLOW	10	6	1.02 [26.0]	.55 [14.0]	.21 [5.3]	.19 [4.8]	.39 [10.0]	.27 [6.9]	YF261CSKIT WITH YF2610D DIE
YFTW0814DL	RED	8	10	1.02 [26.0]	.55 [14.0]	.27 [6.8]	.25 [6.4]	.51 [13.0]	.28 [7.2]	YF261CSKIT WITH YF864D DIE
YFTW0614DL	BLUE	6	16	1.18 [30.0]	.55 [14.0]	.34 [8.7]	.33 [8.3]	.72 [18.4]	.38 [9.6]	

REV	DATE	DESCRIPTION	EC	BY	C'H'K.
A	04/05/2021	NEW DRAWING CREATION	210405006822	SS	YR



NOTES:

1. MATERIAL: COPPER.
2. FINISH : TIN PLATED
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
4. UL LISTED BARE AND COVERED FERRULES PER UL486F REQUIREMENTS.
5. ITEMS WITH CATALOG NUMBERS FOLLOWED BY ASTERISKS (*) ARE NOT UL LISTED.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-387-6487 FOR PRODUCT INFO: http://www.burndy.com	INSULATED FERRULES			
	ITEM NO: SEE TABLE			
	CAT. NO: SEE TABLE			
	DRAWN BY: M.SAURABH 12/07/2020		 	
	CHECKER: K.HERNANDEZ 10/18/2022			
	DSN APRVL: K.HERNANDEZ 10/18/2022			
	MFG APRVL: --			
	QA APRVL: J.BRODEUR 05/10/2021			
	MKT APRVL: A.FITZGER 05/12/2021			
	PROD FAM: --		DRAWING NO	
PROJECT #:		SIZE	50111876	A
DOCUMENT TYPE: SALES		D	SHEET 6 OF 6	
REL LEVEL: Released				