Part Number : 192130010
Product Description : Avikrimp Wire Pin Terminal for 22-18 AWG Wire, Mylar Tape Carrier
Series Number : 19213
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : WP-8218T
Packaging Alternative : 192130009 (Bag)



Documents and Resources

Drawings

192130010_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-011-001.pdf

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	19213
Description	Avikrimp Wire Pin Terminal for 22-18 AWG Wire, Mylar Tape Carrier
Application	Wire-to-Component
Comments	Pin Length 8.90mm
Product Name	Wire Pin,Avikrimp
UPC	800753053502

Agency

CSA	LR18689
UL	E32244

Physical

Flammability	94V-2
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.833/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	1.016µm
Termination Interface Style	Crimp or Compression

Downloaded from Arrow.com.

Wire Insulation Diameter	3.56mm max.
Wire Size (AWG)	18, 19, 20, 22
Wire Size mm^2	N/A

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880023
Mini-Mac Pneumatic Applicator for Ring and Spade Terminals, 22-18 AWG	638851300

Downloaded from Arrow.com.