

## Har-speed M12 malecont. Crimp AWG 23-26



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9019
Specification	Har-speed M12 malecont. Crimp AWG 23-26
HARTING eCatalogue	<a href="https://harting.com/21011009019">https://harting.com/21011009019</a>

### Identification

Category	Contacts
Series	har-speed
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section (mm <sup>2</sup> )	0.13 ... 0.25 mm <sup>2</sup>
Conductor cross-section (AWG)	AWG 26 ... AWG 23
Performance level	1

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	100
Net weight	0.02 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140136717
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522