

TP1038, Vinyl Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [TP1038](#)



Vinyl Ring Terminal For 12 - 10 AWG

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serrations in the inner barrel provides added holding strength and better conductivity

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Buy American Compliant	Yes
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	<ul style="list-style-type: none"> Buy America Compliant (All status valid till December 2025) Buy American Act Compliant (All status valid till December 2025) BABA Compliant (All status valid till December 2025)
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type Ring Terminal

Current

Voltage - Maximum 600 V

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	33 mm
Dimension - Pad Width inch	0.53 in
Package Height	0.000 in
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.40 in
Dimension - Strip Length inch	19/64 in
Dimension - Stud Size inch	3/8 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Z inch	0.45 in
Dimension - Bolt Size fraction	3/8
Cable Insulation Diameter Maximum	0.260 in
Dimension - Length Overall inch	1.3 in
Dimension - Diameter Max Size inch	0.28 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Sub Brand	VINYLUG
Color Code	Yellow
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Style	Shrouded
Type	Ring Tongue
UPC 12 Digit	781810711446
UPC 14 Digit GTIN	00781810711446
Material	Copper
Plating Type	Tin
UPC	781810711446

Logistics

Minimum Pack Quantity 50
Carton Quantity 600
Pallet Quantity 99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-TP1038-SPEC-EN | REV 4/2026