

Plugs

VST 20



Product	VST 20
description	Fully mating connector as built-in pin, solder connection up to maximum cable cross-section of 2 mm ² . Nickel-plated brass contact material.
operating instruction	BA417
Articlenumber	930050000 Ni
drawing	
technical data	
connection	M4 thread, solder connection
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	16 A
material plug	brass, nickel plated
temperature range acc. To IEC61010 ⁽¹⁾	-25 °C to +100 °C

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains
stand: 21.06.2022

stand: 21.06.2022

4 mm system