

Part Number : [192210226](#)

Product Description : Compression Style Ring
Tongue Terminal for 8 AWG Wire, Stud Size 3/8" (M9),
Plated, Wide Pad, Carton

Series Number : 19221

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : BCL-838-WP-PL



Documents and Resources

Drawings

[192210226 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications


[PS-19901-017-001.pdf](#)

[PS-19902-013-001.pdf](#)

[PS-19902-017-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19221
Description	Compression Style Ring Tongue Terminal for 8 AWG Wire, Stud Size 3/8" (M9), Plated, Wide Pad, Carton
Comments	Heavy Duty
Keyword	Ring Terminal, Ring Terminals
Product Name	Battery Cable Lug
Style	Ring, Plated
Type	Battery Cable Lug
UPC	800753062252

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None

Material - Plating Mating	Tin
Net Weight	6.038/g
Packaging Type	Carton
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size (AWG)	8
Wire Size mm ²	8.36

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG	192840034
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	192860117
Die Set (Large) for the HMLS Hydraulic Crimper	192900001
Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals	192940008
Square "DIN" style dies for 8 AWG	640037670
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	638162000

This document was generated on Dec 16, 2025