



Part Number : 1301080170

Series Number : 130108

Product Category : Lamps and Lights

Product Description : Watertite Wet Location
13W Fluorescent Hand Lamp with Switch,
Cord Type 16/3 SJOW, Cord Length 7.62m
(25.0')

Status : Active

Engineering Number : 1913SA

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130108

Description	Watertite Wet Location 13W Fluorescent Hand Lamp with Switch, Cord Type 16/3 SJOW, Cord Length 7.62m (25.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Family	Wide-Area Lighting Products
Product Name	Watertite
Type	Wide Area Lamps
UPC	78678829022

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	13W
Lumens	900
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SJOW
Depth	69.85mm (2.750")
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	N/A
Lamp Type	PL13/41
Length	444.50mm (17.500")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Outlet	None

Packaging Type	Carton
----------------	--------

This document was generated on May 04, 2024