



**Part Number :** [1301550166](#)

**Product Description :** Watertite Extreme Connector with California Style Locking Blade, 2 Pole/3 Wire, Non-NEMA, 480V, Cord Grip Body Size F5

**Series Number :** 130155

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** CS84W64



---

## Documents and Resources

### Drawings

[1301550166 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130155
Description	Watertite Extreme Connector with California Style Locking Blade, 2 Pole/3 Wire, Non-NEMA, 480V, Cord Grip Body Size F5
IP Rating	IP67
NEMA Configuration	Non-NEMA Locking CA
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678801462

### Agency

CSA	LR6837
UL	E10176

### Electrical

Current - Maximum per Contact	50.0A
GFCI	No
Voltage - Maximum	480V

### Physical

Cord Grip Body Size	F5 1 1/4"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes

Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on May 27, 2026