

**3M Touch Systems****Touchscreen Products**

- + Multi-Touch Displays
- + Multi-Touch Systems
- + Touch Systems
- + Touch Displays
- + Touch Controllers
- Touch Software
- Touch System Selector

Touchscreen Applications

- Gaming
- Retail
- Financial
- Transportation
- Entertainment
- Industrial
- Healthcare

Touchscreen Technologies

- Technologies
- Electronics
- Materials
- Manufacturing

Information

- About 3M Touch Systems
- Events
- + Media Center
- Technology and Application Briefs
- Product and Technical Documents
- Warranty Statement

Support

- Touchscreen Drivers
- Customer Service
- + Contact Us
- + Technical Services

[3M Touch Systems Catalog](#) > [Touch Systems](#) > [3M™ MicroTouch™ SCT3250EX System and SCT3250 Sensors](#) >

3M™ MicroTouch™ System SCT3250EX 10.84" Surface Capacitive USB Touch System, Standard aspect ratio

[\[click to enlarge\]](#)

The 3M™ MicroTouch™ System SCT3250EX (surface capacitive touch technology) provides fast, accurate and reliable touch response with operation unaffected by on-screen contaminants and offers premium optical characteristics.

3M ID: 17-8021-217 (98-0003-2506-2)**Status:** Alternate Product (Lead Times Apply)[<< View other configurations of this product](#)

Viewing Area Dimension	Outer Area Dimension	Controllers Available	Aspect Ratio	Cable Length inches (mm)	Cable Exit	Where to Buy
D = Diagonal W = Width H = Height	D = Diagonal W = Width H = Height	UC = USB SC = Serial				
D: 10.84" (275.08 mm) W: 8.58" (217.93 mm) H: 6.61" (167.89 mm)	D: 11.62" (295.15 mm) W: 9.2" (233.68 mm) H: 7.1" (180.34 mm)	Included (EXII-7710UC/98-0003-2216-8)	Standard	4.27" (108.46 mm)	8:00	Select a Region 

Aspect Ratio: Standard**Controller:** USB**EU RoHS Compliant:** Yes [View Certificate](#)**Glass Thickness inches (mm):** 0.125 (3.18)**Precision Area Height inches (mm):** 6.25 (158.75)**Sensor Drawing:** [PDF 89.0K](#)**Cable Termination:** 5 pin**Controllers Available:** Included (EXII-7710UC/98-0003-2216-8)**Etch:** AG500**Precision Area Diagonal inches (mm):** 10.23 (259.84)**Precision Area Width inches (mm):** 8.1 (205.74)**Touch Technology:** 3M Surface Capacitive