



**Part Number :** [1301510014](#)

**Product Description :** Super-Safeway Adapter  
NEMA 5-15 Receptacle - Female End 15A/125V, NEMA  
L5-15 Plug - Male End, 15A/125V

**Series Number :** 130151

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** 1705



---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375- DC (05 Nov 2025)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130151
Description	Super-Safeway Adapter NEMA 5-15 Receptacle - Female End 15A/125V, NEMA L5-15 Plug - Male End, 15A/125V
IP Rating	IP67
NEMA Configuration	NEMA L5-15
Product Name	Super-Safeway
Specialty	N/A
Type	Adapter
UPC	78678875006

### Agency

CSA	LR6837
UL	E10176

### Electrical

Current - Maximum per Contact	50.0A
GFCI	No
Voltage - Maximum	125V

### Physical

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male-Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes

Net Weight	1959.000/g
Poles	2-pole/3-wire
Receptacle Type	N/A

---

This document was generated on Dec 29, 2025