

Representative Image

Catalog No. LTC050

Description: 1/2IN LT TYPE B COND PVC BLK

UPC No 786210789545

Home > Cable Protection Systems > T&B Liquidtight Fittings > Electrical conduit

Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 1/2 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings

Descriptors

Category	Electrical conduit
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily
Application	Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles.

Specifications

Voltage Rating	600 V
Material	PVC
Color	Black

Classifications

Brand Name	T&B Liquidtight Fittings
Standard	UL E95745, CSA

Dimensions

Trade Size	1/2 in
Outside Diameter	21.3 mm
Inside Diameter	15.8 mm
Length	30.5 m

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

Downloaded from Arrow.com.

ETIM	EC001177 Protective plastic hose
Nominal size in inch	1/2 inch
Flexibility	Flexible
Colour	Black
Approved according to CSA	Y

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	088170	181301	N/A	1239041	N/A
UL	E95745	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.