




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-970108	2009/07/10	Vicky	Remove Pin Dim.
C	LEN1350212	2013/05/14	Yulong	Change the Dimension




Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP68
IP68: 1M of depth of water 24 hours
(防水等級: IP68)
(IP68: 1米水深24小時)
- * Do Mating Test After Glued
點膠後, 須作對插測試
- * Housing: Black, Nylon+GF.
- * Connector: Black, PBT.
- * Male Pin: Copper Alloy, Gold Plated.
- * Ring: Light Blue, Silicone.
- * Screw: Copper Alloy, Nickel Plated, #4-40 UNC.
- * Applicable Wire Range: 22AWG-26AWG.
適用電線範圍: 22AWG-26AWG



Screw L=5.0 For Panel Thickness
Under 1.2mm
適用板厚為 1.2mm 以下

Screw L=6.0 For Panel Thickness
Between 1.2~2.0mm
適用板厚為 1.2~2.0mm



Recommended Panel Cut-Out
建議挖孔尺寸

UNIT: mm		TITLE D-SUB Conn. Panel Screw DB9P M Conn. M Pin		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO SDB-09PMMS-SL8001	DRAWN BY Yulong_wang	DATE 2013-05-14
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 1:1	SIZE A4	SHEET 1 OF 1		DWG NO SDB-09PMMS-SL8001	CHECKED BY Victor	DATE 2013-05-14
REV. C		WC-REV. A.5	QC: Inspection item			CUSTOMER ALTW	APPROVED BY Maslow	DATE 2013-05-14

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.