



Part Number : [2263921023](#)

Product Description : Zero-Hachi-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, Tin (Sn) Plating, 2 Circuits, 300.00mm Length, Black

Series Number : 226392

Status : Active

Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

[2263921023 sd.pdf](#)

3D Models and Design Files


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|------------------------|--|
| Status | Active |
| Category | Power and Signal Cable Assemblies |
| Series | 226392 |
| Description | Zero-Hachi-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, Tin (Sn) Plating, 2 Circuits, 300.00mm Length, Black |
| Application | Power, Wire-to-Board |
| Assembly Configuration | Single Ended Connector |
| Connector to Connector | Zero-Hachi Terminal-to-Pigtail |
| Product Name | Zero-Hachi |
| Type | Discrete Wire Assembly |
| UPC | 198282215929 |

Electrical

| | |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum | 30V AC (RMS)/DC |

Physical

| | |
|--------------------|----------------|
| Cable Length | 300.00mm |
| Circuits (Loaded) | 2 |
| Circuits (maximum) | 2 |
| Color - Resin | Black |
| Gender | Female-Pigtail |

| | |
|--------------------------------|------------------------------|
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Matte Tin |
| Material - Plating Termination | Matte Tin |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Net Weight | 0.980/g |
| Number of Rows | 1 |
| Overmolded | No |
| Packaging Type | Bag |
| Pitch - Mating Interface | 0.80mm |
| Plating min - Mating | 1.000µm |
| Plating min - Termination | 1.000µm |
| Single Ended | No |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | UL 10064 |
| Wire Size (AWG) | 28 |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|---|-------------------------------|
| Zero-Hachi Right-Angle Single Row Headers | <u>214721</u> |

This document was generated on Apr 30, 2026