

SAGA-S-WHT

~30° spot beam

TECHNICAL SPECIFICATIONS:

Dimensions	Ø 50.0 mm
Height	13.7 mm
Fastening	screw
ROHS compliant	yes 


MATERIAL SPECIFICATIONS:

Component	Type	Material	Colour	Finish
SAGA-S	Single lens	Silicone	clear	
SAGA-FRAME-WHT	Holder	HRPC		

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
FCA14933_SAGA-S-WHT	Single lens	630	70	35	10.4
» Box size: 480 x 280 x 300 mm					









PHOTOMETRIC DATA (MEASURED):



LED CXA/B 15xx
FWHM 26.0°
Efficiency 94 %
Peak intensity 2.700 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED CXA/B 1816 & CXA/B 1820 & CXA 1850
FWHM 34.0°
Efficiency 94 %
Peak intensity 1.650 cd/lm
LEDs/each optic 1
Light colour White
Required components:




PHOTOMETRIC DATA (SIMULATED):




LED VERO10
FWHM 21.0°
Efficiency 97 %
Peak intensity 3.754 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED CXA/B 13xx
FWHM 15.0°
Efficiency 94 %
Peak intensity 7.100 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED LC010C
FWHM 30.0°
Efficiency 91 %
Peak intensity 3.400 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 479 Typ L6




LED LC020C
FWHM 36.0°
Efficiency 88 %
Peak intensity 2.200 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 479 Typ L6



PHOTOMETRIC DATA (SIMULATED):

SAMSUNG

LED LC040C
FWHM 44.0°
Efficiency 87 %
Peak intensity 1.400 cd/Im
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 480 Typ L6



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)