

## SKINDICHT® BL-M

SKINDICHT® BL-M, brass blind plugs for closing pre-threaded holes, assembling with screwdriver



Corrosion-resistant



Robust



Reliability



Temperature-resistant

### Benefits

For closing pre-threaded holes  
Assembling with screwdriver

### Application range

Machine and equipment manufacturing  
Electric motor manufacturing

### Product Make-up

Metric connection thread acc. to DIN EN 60423  
Basis for technical information DIN IEC 62444

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 Class-Description: Plug for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class-Description: Plug for cable screw gland

On request:

Fitted with FKM O-ring

Last Update (22.09.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINDICHT® BL-M

|                    |                                                                 |
|--------------------|-----------------------------------------------------------------|
| Material:          | Body: nickel-plated brass                                       |
| Protection rating: | IP 54<br>IP 68 (with O-Ring)                                    |
| Temperature range: | With O-ring: -30°C to +100°C<br>Without O-ring: -60°C to +200°C |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

# SKINDICHT® BL-M

| Article number              | Article designation / size | Outer Ø (mm) | Pieces / PU |
|-----------------------------|----------------------------|--------------|-------------|
| SKINDICHT® BL-M             |                            |              |             |
| 52103100                    | M 12 x 1,5                 | 14.0         | 100         |
| 52103110                    | M 16 x 1,5                 | 18.0         | 100         |
| 52103120                    | M 20 x 1,5                 | 22.0         | 100         |
| 52103130                    | M 25 x 1,5                 | 28.0         | 100         |
| 52103140                    | M 32 x 1,5                 | 35.0         | 50          |
| 52103150                    | M 40 x 1,5                 | 44.0         | 25          |
| 52103160                    | M 50 x 1,5                 | 54.0         | 10          |
| 52103170                    | M 63 x 1,5                 | 70.0         | 10          |
| 52103190                    | M 75 x 1,5                 | 80.0         | 1           |
| SKINDICHT® BL-M with O-ring |                            |              |             |
| 52103105                    | M 12 x 1,5                 | 14.0         | 100         |
| 52103115                    | M 16 x 1,5                 | 18.0         | 100         |
| 52103125                    | M 20 x 1,5                 | 22.0         | 100         |
| 52103135                    | M 25 x 1,5                 | 28.0         | 100         |
| 52103145                    | M 32 x 1,5                 | 35.0         | 50          |
| 52103155                    | M 40 x 1,5                 | 44.0         | 25          |
| 52103165                    | M 50 x 1,5                 | 54.0         | 10          |
| 52103175                    | M 63 x 1,5                 | 70.0         | 10          |

Last Update (22.09.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16