



Material Datasheet

22.05.2023

TULT9-3YE
Article Number 553-40950



Material: Polyolefin, cross-linked (PO-X)
Colour: Yellow (YE)

Supplied Ø D: 9.0 mm
Recov. Ø d: 3.0 mm
Wall (WT): 0.64 mm
Shrink Ratio: 3:1
Minimum Shrink Temperature - °C: +90 °C

Test Method

Flammability: UL 224 VW-1
Operating Temperature : -55 °C to +135 °C

Dielectric Strength: 37 kV/mm
Insulation Class: B (VDE 0530)
ASTM D876

Longitudinal Change After Shrinkage: -15% max.

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved



Material Datasheet

22.05.2023

Print Method:

Thermal transfer print

Print Method (Alternative):

Laser beam print

Application Tool:

H6100, TT431, TT4030, TrakMark DS



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved