

# GJM1551C1H9R4WB01#

“#” indicates a package specification code.





## < List of part numbers with package codes >

GJM1551C1H9R4WB01D

GJM1551C1H9R4WB01W

GJM1551C1H9R4WB01J

## Appearance & Shape



## References

| Packaging | Specifications          | Standard Packing Quantity |
|-----------|-------------------------|---------------------------|
| D         | 180mm Paper Tape        | 10000                     |
| W         | 180mm Paper Tape (W8P1) | 20000                     |
| J         | 330mm Paper Tape        | 50000                     |

| Mass (typ.) |       |
|-------------|-------|
| 1 piece     | 1.6mg |
| φ180mm Reel | 118g  |

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GJM1551C1H9R4WB01#

“#” indicates a package specification code.



## Specifications

|                                                  |                |
|--------------------------------------------------|----------------|
| Length                                           | 1.0±0.05mm     |
| Width                                            | 0.5±0.05mm     |
| Thickness                                        | 0.5±0.05mm     |
| Capacitance                                      | 9.4pF ±0.05pF  |
| Distance between external terminals g            | 0.3mm min.     |
| External terminal size e                         | 0.15 to 0.35mm |
| Operating Temperature Range                      | -55°C to 125°C |
| Rated Voltage                                    | 50Vdc          |
| Size code in inch(mm)                            | 0402 (1005M)   |
| TC                                               | 0±30ppm/°C     |
| Temperature characteristics (complied standard)  | CG(JIS)        |
| Temperature range of temperature characteristics | 20°C to 125°C  |

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.