
Part Number : 351810220
Product Description : VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type C, Natural
Series Number : 35181
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

351810220_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

351810200-100.pdf

PS-35182-003-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	35181
Description	VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type C, Natural
Application	Wire-to-Wire
Component Type	Housing
Product Name	VersaBlade
UPC	800754376112

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)

Downloaded from Arrow.com.

Net Weight	1.700/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	8.00mm
Pitch - Termination Interface	8.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
VersaBlade Multi-Module 2-2-2 Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural	351800600
VersaBlade Multi-Module 2-2-2 Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable	351800609
VersaBlade Multi-Module 2-2-2 Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Yellow, Glow-Wire Capable	351803609
VersaBlade Multi-Module 2-2-2 Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue, Glow-Wire Capable	351804609

Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 1 Circuit, Natural	351820190
VersaBlade Terminal Position Assurance (TPA) Retainer, 1 Circuit, Red	351820192

Downloaded from Arrow.com.

VersaBlade Terminal Position Assurance (TPA) Retainer, 1 Circuit, Yellow	351820193
VersaBlade Terminal Position Assurance (TPA) Retainer, 1 Circuit, Blue	351820194
VersaBlade Female Crimp Terminal, 24-22 AWG, Type C	2270298400
VersaBlade Female Crimp Terminals	35748

Downloaded from Arrow.com.