



Technical data	
Memory	2 GB (SLC)
Write/read cycles (max.)	17 MB/s / 20 MB/s
MTBF	4,000,000 h
Service life	per Cell: 100.000 write cycles

Physical data	
Width	15 mm
Height	11 mm
Depth	1 mm

Material data	
Fire load	0 MJ
Weight	4.6 g

Environmental requirements	
Ambient temperature (operation)	-40 ... +90 °C
Ambient temperature (storage)	-40 ... +90 °C
Relative humidity (without condensation)	95 %
Vibration resistance	15g
Shock resistance	50g

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	TW
GTIN	4055143389815
Customs tariff number	85235110000



Product classification	
UNSPSC	43202005

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 758-879/000-3102	