



+ CONNECTORS

RECTANGULAR CONNECTOR HOODS



✓ Active

TE CONNECTIVITY (TE)
HB.6.STS.1.M20.G
[HDC](#) | [HDC Hood & Housings](#) , [HDC IP 65 Hood & Housing](#)

[1106419-7](#)
TE Internal Number: 1106419-7

[EU RoHS Compliant with Exemptions](#)
[EU ELV Compliant with Exemptions](#)

Accessory Type Hood

Entry Style Side

Locking Device Type Side Clip

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

HOOD HB6

PDF
English

CAD Files

3D PDF

PDF
3D

Customer View Model

2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Accessory Type Hood

Product Size 3

Product Type Accessory

Thread Size M20

HTS Housings and Hoods Yes

Body Features

Entry Style Side

Color Gray

Material Aluminum

Mechanical Attachment

Locking Device Type Side Clip

Locking Device Location Housing Bottom

Dimensions

Height 48 mm [1.886 in]

Width 43 mm [1.689 in]

Length 60 mm [2.357 in]

Usage Conditions

Corrosion Protected No

Packaging Features

Packaging Quantity 5

Packaging Method Box

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF

