Part Number : 936010414
Product Description : Heavy-Duty Turned Crimp Contact for 40A Modules, Female, Silver (Ag) Plated Copper Alloy, 10.00mm² (7 AWG), 100 per Bag
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Contacts
Engineering Part Number : 7600.5704.0



Documents and Resources

Drawings

936010414_sd.pdf

Specifications

936010406-S00.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Contacts
Series	93601
Description	Heavy-Duty Turned Crimp Contact for 40A Modules, Female, Silver (Ag) Plated Copper Alloy, 10.00mm² (7 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Name	Heavy-Duty Connectors
UPC	887191889221

Agency

CSA	256883
UL	E249674

Electrical

Current - Maximum per Contact	40.0A

Physical

Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	2.260/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	15.00mm

Downloaded from Arrow.com.

Wire Size (AWG)	7
Wire Size mm^2	10.00

Mates With / Use With

Mates with Part(s)

Description	Part Number
Heavy-Duty Connectors and Accessories	93601

Use with Part(s)

Description	Part Number
Use With	S-M Modules

Downloaded from Arrow.com.