





ELECTRICAL SPECIFICATIONS

FREQUENCY RANGE (GHz):	17.0 - 20.0
ISOLATION (dB):	22 MIN
INSERTION LOSS (dB):	0.40 MAX
VSWR:	1.20 MAX
POWER: AVG (PORT 1 TO 2):	10W
REFLECTIVE POWER (TERM):	2W
PEAK:	50W

MECHANICAL SPECIFICATIONS

CONNECTORS:	SMA-FEMALE, PASSIVATED STAINLESS STEEL
CONTACT PINS:	BERYLLIUM COPPER, GOLD PLATE
OPERATING TEMPERATURE:	-20° to +65°C
WEIGHT (APPROX):	0.74 OUNCES

DIMENSIONS IN INCHES, UNLESS OTHERWISE SPECIFIED		 Fresno, California, USA	
TOLERANCE	XX±0.03 XXX±0.010	TITLE	
SCALE		17.0 - 20.0GHz SMA Isolator	
6:1		MODEL NO	REV
		D3I1720	