

# Product data sheet

Specifications



## APC NetShelter CX, Replacement Power Supply, C14 Socket, 24V

AR4705

⚠ Discontinued on: 30 June 2023

⚠ To be discontinued

### Overview

Lead time Usually in Stock

### Main

|                       |                    |
|-----------------------|--------------------|
| Main Input Voltage    | 100 V              |
|                       | 110 V              |
|                       | 115 V              |
|                       | 120 V              |
|                       | 127 V              |
|                       | 200 V              |
|                       | 208 V              |
|                       | 220 V              |
|                       | 230 V              |
|                       | 240 V              |
| Main Output Voltage   | 24 V DC            |
| Input Connection Type | IEC 60320 C14      |
| Provided equipment    | Installation guide |

### Physical

|                     |                       |
|---------------------|-----------------------|
| Height              | 1.26 in (3.2 cm)      |
| Width               | 2.05 in (5.2 cm)      |
| Depth               | 4.57 in (11.6 cm)     |
| Product Weight      | 0.77 lb(US) (0.35 kg) |
| Mounting preference | No preference         |
| Mounting Mode       | Not rack-mountable    |

### Input

Input Frequency 50/60 Hz +/- 3 Hz auto-sensing

### Conformance

|                        |                  |
|------------------------|------------------|
| Product Certifications | C-tick           |
|                        | CCC              |
|                        | PSE              |
|                        | cUL Listed       |
| Standards              | EN 55022 Class B |
|                        | EN 55024         |
|                        | EN 61000-3-2     |
|                        | EN 61000-3-3     |
|                        | EN 61000-4-8     |
|                        | EN/IEC 60950-1   |

EN 61000-4-2  
EN 61000-4-3  
EN 61000-4-4  
EN 61000-4-6

Ordering and shipping details

GTIN731304336051

Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 3.94 in (10 cm)      |
| Package 1 Width              | 5.12 in (13 cm)      |
| Package 1 Length             | 7.09 in (18 cm)      |
| Package 1 Weight             | 1.32 lb(US) (0.6 kg) |

Offer Sustainability

|                    |                                                                                                   |
|--------------------|---------------------------------------------------------------------------------------------------|
| REACH Regulation   | <a href="#">REACH Declaration</a>                                                                 |
| REACH free of SVHC | Yes                                                                                               |
| EU RoHS Directive  | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
| Take-back          | Take-back program available                                                                       |

Contractual warranty

Warranty2 year (manufacturer's defect)

Recommended replacement(s)