





REV.	DATE	DESCRIPTION
B	10/22/98	ADD HEX NUT AND MOUNTING HOLE DIMS.



RECOMMENDED
MOUNTING HOLE

DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY			APPROVALS	DATE	TITLE			
1 BODY	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4			DRAWN	10/22/98	BNC FEMALE TO MALE PUSH ON ADAPTOR 75ohms			
2 INSULATOR	TEFLON	NATURAL				CHECKED					
3 CONTACT PIN	PHOS. BRONZE	GOLD				ISSUED					
4 NOTE: GOLD PLATING AT 50u MIN.											
5 HEX NUT	BRASS	NICKEL						SIZE	FSQM NO.	DWG. NO.	REV.
6								A	99001	112532.DWG	B
7								SCALE	NA	PART NO.	SHEET
8			DO NOT SCALE DRAWING							112532	1 OF 1

connex
Connector Corporation