

HIGH STR. FO CABLE-MM-2CH.-20M,RING




Image is for illustration purposes only. Please refer to product description.

Part number	33 58 751 0200 001
Specification	HIGH STR. FO CABLE-MM-2CH.-20M,RING
HARTING eCatalogue	https://b2b.harting.com/33587510200001

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	FO cable
Description of the cable	Multimode

Version

Cable length	20 m
Core structure	62.5 / 125 µm

Technical characteristics

Cable diameter	7 mm
----------------	------

Material properties

Material (cable)	PUR (polyurethane)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	750 g
Net weight	36 g/m
Country of origin	Germany
European customs tariff number	85444995
eCl@ss	27061803 Fiber optic cable