

Item number 28.0039- *

Technical data	
Diameter of plug system	2 mm
Rated Values	30 V, 10 A / 60 V, 10 A
Surface treatment electrical contact	Au
Base material electrical contact	CuZn
Standard color(s) *	21 22 23 24 25 27 28 29
Optional color(s)	26
Lead lengths	007; 015; 030; 045; 050; 060 cm
Lead insulation	PVC
Lead cross section	0,5 mm²
Test accessory acc. to	IEC EN 61010-031
User-Information	I 093