

# Specifications

## Eaton DR73-820-R



Eaton DR inductor, 80.4  $\mu$ H, 0.86 A Irms, 0.89 A ISAT, 448 m $\Omega$  resistance, SMT mounting, Ferrite, 2-pins, 1350 qty.

Photo is representative



### General specifications

PRODUCT NAME	Eaton DR73 inductor
CATALOG NUMBER	DR73-820-R
UPC	051712888820
EAN	5027590169103
PRODUCT LENGTH/DEPTH	7.6 mm
PRODUCT HEIGHT	3.55 mm
PRODUCT WIDTH	7.6 mm
PRODUCT WEIGHT	0.609 g
COMPLIANCES	RoHS Compliant

## Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.86 A
ISAT	0.89 A
PACKAGE QUANTITY	1350
MATERIAL	Ferrite
AUTOMOTIVE GRADE	No
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	448 mΩ
TERMINALS	7.5x7.5x3.35mm
SERIES	DR73

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton DR high power density high efficiency shielded drum core power inductors data sheet](#)

[Eaton Specification Sheet - DR73-820-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

