

WI-M-8-XX-@

(Extra Heavy-duty 8 AWG, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-8 is "Coolflex 50" wire that is 8 AWG, 1650/0.08 stranded, tinned copper wire with highly flexible 0.236" (6mm) diameter silicone jacket.
- Ratings: Current 50 Amps @ 105°C
 Voltage 600V
- Length: The "XX" in the model number indicates length in feet.
 Standard lengths: 10', 25', 30', *50', *100'
 (custom lengths available upon request)
 * = **Sold as spooled wire**
- Color: The "@" in the model number represents color.
 Available colors: -0 Black, -2 Red
- RoHS 3 compliant