

Part Number : [1301530039](#)

Series Number : 130153

Status : Preliminary

Engineering Number : 15050-6TT



Drawings

[1301530039_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

Part Details

General

Status	Preliminary
Category	Power Distribution
Series	130153
Description	Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Molded NEMA 5-15 Tri-Tap, 15A, 120V, 1.83m (6.0') Cord Length
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Name	Safeway
Type	GFCI Commercial Duty, Single Phase
UPC	78678828429

Agency

CSA	LR6837
UL	E66308

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	120V AC

Physical

Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	1.83m (6.0')
Cord Type	12/3 SJTW
Feed-Thru	Yes
Flip Lid	No

Material - Housing	Nylon
Mounting Style	Portable
Number of Receptacles	3
Packaging Type	Bag
Receptacle Type	N/A

This document was generated on Sep 24, 2025