
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A5	NEW RELEASE	17/AUG/2022	
A6	Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A7	CHANGE CABLE PRINTING	28/JULY/2025	



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80°C 300V
26AWG VW-1 LL84201 CSA AWM I/II A 80°C 300V 26AWG FT1 COPARTNER

NOTE:
1. TESTING CONDITIONS:
   A: INSULATION RESISTANCE: 10MΩ
   B: VOLTAGE: DC300V/0.01S
   C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω
2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°,
   DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT

P1	P2		P1	P2	
1	1	BLACK	15	15	RED/WHITE
2	2	BROWN	16	16	ORANGE/WHITE
3	3	RED	17	17	GREEN/WHITE
4	4	ORANGE	18	18	BLUE/WHITE
5	5	YELLOW	19	19	PURPLE/WHITE
6	6	GREEN	20	20	RED/BLACK
7	7	BLUE	21	21	ORANGE/BLACK
8	8	PURPLE	22	22	YELLOW/BLACK
9	9	GREY	23	23	GREEN/BLACK
10	10	WHITE	24	24	GRAY/BLACK
11	11	PINK	25	25	PINK/BLACK
12	12	LIGHT GREEN	26	26	PINK/RED
13	13	BLACK/WHITE	SHELL	SHELL	DRAIN
14	14	BROWN/WHITE			

P/N CHART

ACD P/N	LENGTH±T	
CS-DSDHD26MF0-001.6	1.6FT±1.0inch	488±25mm
CS-DSDHD26MF0-002.5	2.5FT±1inch	762±25mm
CS-DSDHD26MF0-005	5FT±2inch	1524±51mm
CS-DSDHD26MF0-010	10FT±3inch	3048±76mm
CS-DSDHD26MF0-015	15FT±3inch	4572±76mm
CS-DSDHD26MF0-025	25FT±4inch	7620±102mm
CS-DSDHD26MF0-050	50FT±8inch	15240±203mm

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
DECIMALS .X ±.X .XX ±.XX .XXX ±.XXX
ANGLES ±X°
THIRD ANGLE PROJECTION

EAR NO.

APPROVALS	DATE
DRAWN XF	
CHECKED HYJ	
RESP ENG	
MFG ENG	

CAD FILE:

Amphenol Cables on Demand
20 VALLEY ST. ENDICOTT, NY 13760

DELUXE HDB26M/F MOLDED

SIZE A | DWG. NO. CS-DSDHD26MF0-XXX | REV. A7

SCALE: N/A | SHEET 1 OF 1

NOTES: UNLESS OTHERWISE SPECIFIED

Downloaded from Arrow.com.