



Δ

D




REV F - 2006-04-17



STANDARD LAYOUT FOR 'KEEP OUT ZONE' (Connector Side)



Hatching area might be free of components
Maximum free space outside of these zones = 5.5 mm

EUROPEAN PROJECTION



www.fciconnect.com			surface 		tolerance std		projection 		mm 		
			ISO 1302		ISO 406 ISO 1101						
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	N.TWINCY	2002/04/30	ANGULAR	LINEAR	0.X	±	size	A3	Scale	3:2	
Eng	F TISSERAND	2002/04/30			0.XX	±					
Chr	RAMESH P.K	2009/03/26	0° ±°		0.XXX	±	ECN		109-0048		
Appr	S.S.CHERIAN	2009/03/26	Product family			5S2F	Spec ref		SEE NOTES		
		title L26 TYPE F02				dwg no L26_TYPE_F02				Rev. F	
		catalog no SEE TABLE				CUSTOMER				sheet 2 of 2	