

Specifications



Photo is representative



Eaton RL1011-152-R

Eaton RL1011 inductor, 1499 μ H, 0.324 A I_{rms} , 0.39 A ISAT, 3000 m Ω resistance, THT mounting, Ferrite, 2-pins, 800 qty.

General specifications

PRODUCT NAME	Eaton RL1011 inductor
CATALOG NUMBER	RL1011-152-R
UPC	051712497909
PRODUCT LENGTH/DEPTH	9.5 mm
PRODUCT HEIGHT	10.5 mm
PRODUCT WIDTH	9.5 mm
PRODUCT WEIGHT	2.5 g
COMPLIANCES	RoHS Compliant



Powering Business Worldwide

Product specifications

TYPE	Inductor
MOUNTING	THT
IRMS	0.324 A
ISAT	0.39 A
PACKAGE QUANTITY	800
MATERIAL	Ferrite
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	3000 mΩ
SERIES	RL1011

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton RL1011 unshielded radial leaded drum core inductors data sheet](#)

[Eaton Specification Sheet - RL1011-152-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

