





| SPECIFICATIONS          |                     |              |
|-------------------------|---------------------|--------------|
| PARAMETERS              | VALUES              | UNITS        |
| RATED VOLTAGE           | 24                  | Vdc          |
| OPERATING VOLTAGE RANGE | 15 ~ 27             | Vdc          |
| RATED CURRENT (MAX)     | 30                  | mA           |
| MINIMUM SPL @ 10 CM     | 84                  | dBA          |
| RESONANT FREQUENCY      | 400 ± 50            | Hz           |
| TONE OR PULSE RATE      | CONTINUOUS          | 0 pulse /sec |
| OPERATING TEMPERATURE   | -20 ~ +65           | °C           |
| STORAGE TEMPERATURE     | -30 ~ +75           | °C           |
| HOUSING MATERIAL        | ABS                 | -            |
| TERMINAL MATERIAL       | Sn PLATED<br>COPPER | -            |
| WEIGHT                  | 8.5                 | grams        |


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.  
©2003, Projects Unlimited Inc.

| REVISION HISTORY |                                          |           |          |
|------------------|------------------------------------------|-----------|----------|
| LTR              | DESCRIPTION                              | DATE      | APPROVED |
| -                | RELEASED FROM ENGINEERING                | 5/29/2007 |          |
| A                | REVISED TO INVENTOR 3-D DRAWING TEMPLATE | 3/11/2008 | B.R.     |
| B                | REVISED SPL, ROHS STATUS                 | 9/23/13   | M.L.     |



NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2011/65/EU COMPLIANT.

|                                                                                                                  |      |                                                                                                                                              |           |            |                    |             |           |            |         |
|------------------------------------------------------------------------------------------------------------------|------|----------------------------------------------------------------------------------------------------------------------------------------------|-----------|------------|--------------------|-------------|-----------|------------|---------|
| UNLESS OTHERWISE SPECIFIED:<br><br>DIMENSIONS ARE IN MILLIMETERS,<br><br>TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°. | SIZE | Designed by                                                                                                                                  | Date      | Checked by | Date               | Approved by | Date      | Drawn Date |         |
|                                                                                                                  |      | J.D.                                                                                                                                         | 5/29/2007 | D.F.       | 5/29/2007          | R.W.        | 5/29/2007 | 3/11/2008  |         |
|                                                                                                                  | A3   |  <b>pui audio</b> ™ inc<br>a projects unlimited company |           |            | AI-2304-TT-24V-2-R |             |           |            |         |
|                                                                                                                  |      |                                                                                                                                              |           |            | Indicator          |             |           |            | Edition |
| AI-2304-TT-24V-2-R.idw                                                                                           |      |                                                                                                                                              |           |            |                    | -           | 1 / 1     |            |         |