



Pushing Performance

FO CABLE-SM-2CH.-10M,RING




Image is for illustration purposes only. Please refer to product description.

Part number	33 58 751 0100 002
Specification	FO CABLE-SM-2CH.-10M,RING
HARTING eCatalogue	https://b2b.harting.com/33587510100002

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	FO cable
Description of the cable	Singlemode

Version

Cable length	10 m
Core structure	9 / 125 µm

Technical characteristics

Cable diameter	6.5 mm
----------------	--------

Material properties

Material (cable)	PUR (polyurethane)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance

Commercial data

Packaging size	1
Net weight	360 g
Net weight	36 g/m
Country of origin	Germany
European customs tariff number	85447000
eCl@ss	27061803 Fiber optic cable