Part Number : 2290972222
Product Description : Pre-Crimped Lead Zero-Hachi Female-to-Pigtail, 0.10µm Gold (Au) Plating, 150.00mm Length, 28 AWG, Black
Series Number : 229097
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2290972222_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	229097
Description	Pre-Crimped Lead Zero-Hachi Female-to-Pigtail, 0.10µm Gold (Au) Plating, 150.00mm Length, 28 AWG, Black
Application	Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Zero-Hachi Terminal-to-Pigtail
Keyword	Pre-Crimped Leads
Product Name	Zero-Hachi
UPC	198930256724

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	30V AC (RMS)/DC

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.189/g
Packaging Type	Bag
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm

Downloaded from Arrow.com.

Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10064
Wire Size (AWG)	28

Mates With / Use With

Use with Part(s)

Description	Part Number
Zero-Hachi Single Row Receptacle Housings	214719

Downloaded from Arrow.com.