
55A0811-18-9CK5050 Product Details



Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

55A0811-18-9CK5050

55A0811-18-9CK5050

TE Internal Number: CQ04533001

Pricing & Availability
Request Sample
Add to My Part List
Buy Product through Distributor

Product Highlights View All

- Cable Type = Spec 55
- Wire Source = United Kingdom
- Cable Style = Primary
- Wire Size (AWG/CM) = 18 AWG
- Voltage Rating = 600 VAC

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Cable Type	Spec 55
Cable Style	Primary

Electrical Characteristics

Voltage Rating (VAC)	600

Dimensions

Conductor Outer Diameter (mm [in])	1.27 [0.050]

Body Features

Wire Size (AWG/CM)	18 AWG
Conductor Type	Tin-Coated Copper
Wire Color	White
Nominal Outside Diameter (mm [in])	1.78 [0.070]
Wire Diameter (mm [in])	1.78 [0.070]

Configuration Features

Number of Conductors	1

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Temperature Range (°C)	-65 – +150
Wire Size - Details	18 AWG 0.96 mm², 0.0015 in², 19 x 30 AWG

Operation/Application

Application	Airframe - Normal Weight

Packaging Features

Wire Source	United Kingdom

Other

Brand	Raychem

Related Products

Not quite the product you're looking for?
Find Similar Products

View Part in Product Feature Selector

Check for Tooling

[+] Feedback



© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved | [+] Provide Website Feedback

Downloaded from Arrow.com.