







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C210686	2021/05/12	Vicky	△B X4

Recommended
Panel Cut-Out△B
M8S-XXPFFR-SF8001


XX: No. Of Pin



PCB Layout




3P



4P

Pin Assignments Front View



- △B Note:
- * RoHS Compliant
 - * Ⓢ Important dimension
 - * Waterproof rate: IPX8, unmated 1m/24h
 - * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - O-Ring: Rubber, Green
 - * Shield: Metal
 - * Ground: Metal
 - * Nut: Metal
 - * O-Ring: Rubber, Green
 - * For panel thickness: 2.0~4.5mm
 - * For pcb thickness max: 1.6mm
 - * Nut is packed separately in pe bag

UNIT:mm		TITLE	N SEN, M8-SHLD, SCREW RECEPTACLE, F, F, PCB R		△B
TOLERANCE		SCALE	2:1	SIZE	A4
.X	±0.25	REV.	B	WC-REV.	A.12
.XX	±0.1	SHEET 1 OF 1			QC: Inspection item
.XXX	±0.05				
ANGLES	±1°				

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Yulong_wang	2016-01-20
DWG NO	CHECKED BY	DATE
M8S-XXPFFR-SF8001	Cary	2016-01-20
CUSTOMER	APPROVED BY	DATE
ALTW	Jerry	2016-01-20