

Power Matters.™

[Home](#) ▶ [JAN2N657S](#)

Products

- ▶ [Product Directory](#)
- ▶ [Applications Directory](#)
- ▶ [Parametric Search](#)

JAN2N657S

Overview

Diagrams

Electrical Rating	Symbol	Min	Typ	Max	Unit
DC Current Gain	HFE	30.00		90.00	

Maximum Electrical Rating	Symbol	Min	Typ	Max	Unit
Collector Current (dc)	I_C			0.20	A
Collector-Emitter Voltage (Base Open)	V_{CEO}			100.00	V
Junction Temperature (°C)	T_J			200.00	°C

This part can be found in the following product categories:

• [Power Discretes & Modules](#) ▶ [BJT\(BiPolar Junction Transistor\)](#) ▶ [NPN Transistor](#)

Related Links

[Technical support](#)[How to Buy](#)[Available Stock](#)[Sales Contacts](#)