







Connector Location A

Connector Location B



X
male
(without dust cap and protection cap)

Y
male
(without dust cap and protection cap)



Further information see DS 33265100000

		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved		Created by 402676 Gross	Inspected by 402676 Gross	Standardisation COSTEA Costea	Date 2022-08-31	State Final Release
	Department HCS - RO		Title PP XS LCdx Lg - PP XS LCdx Lg, MM Assy				Doc-Key / ECM-Nr. 100572207/UGD/033/E 500000219506
	HARTING Customised Solutions D-32339 Espelkamp		Type TB	Number 3326231XXX0012		Rev. E	Page 1/2

	1	2	3	4	5	6	7	8
A								
B								
C	27	33262311000012	FO Breakout Cable, MM, 50/125µm, PUR, black, bend tolerant OM3	100	±1%			
	26	33262310900012		90				
	25	33262310800012		80				
	24	33262310700012		70				
	23	33262310600012		60				
	22	33262310500012		50				
	21	33262310450012		45				
	20	33262310400012		40				
	19	33262310350012		35				
	18	33262310300012		30				
	17	33262310250012		25				
	16	33262310200012		20				
	15	33262310150012		15				
	14	33262310140012		14				
	13	33262310130012		13				
	12	33262310120012		12				
	11	33262310110012		11				
	10	33262310100012		10				
	9	33262310090012		9				
	8	33262310080012		8				
	7	33262310070012		7				
	6	33262310060012		6				
	5	33262310050012		5				
	4	33262310040012		4	±0.03			
	3	33262310030012		3				
	2	33262310020012		2				
F	1	33262310010012		1				
	Cont. no.	Part no.	Type of cable	Dim. a[m]	 HARTING Customised Solutions D-32339 Espelkamp All rights reserved Department HCS - RO Created by 402676 Gross Inspected by 402676 Gross Standardisation COSTEA Costea Date 2022-08-31 State Final Release Title PP XS LCdx Lg - PP XS LCdx Lg, MM Assy Type TB Number 3326231XXX0012 Doc-Key / ECM-Nr. 100572207/UGD/033/E Rev. E Page 2/2			