



**Part Number :** 936010526

**Product Description :** Heavy-Duty Crimp Contact Insert, Male, 3-Pole, 40A, for Crimp Contacts, Size «34.2x14.60»



**Series Number :** 93601

**Status :** Active

**Product Category :** Heavy-Duty Connectors

**Engineering Number :** 7703.3266.0

---

## Documents & Resources

### Product Environment Compliance

#### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant                                |
| China RoHS         | ⓘ<br>per SJ/T 11365-2006                    |
| EU ELV             | Not Relevant                                |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21             |
| REACH SVHC         | Not Contained per ED/71/2019 (16 July 2019) |
| EU RoHS            | Compliant per EU 2015/863                   |

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

## Additional Product Compliance Information

### UKCA - Declaration of Conformity

### CE - Declaration of Conformity

## **Part Details**

### **General**

|                |   |
|----------------|---|
| Status         | Active  |
| Category       | Heavy Duty Connectors   |
| Series         | 93601   |
| Description    | Heavy-Duty Crimp Contact Insert, Male, 3-Pole, 40A, for Crimp Contacts, Size «34.2x14.60» |
| Component Type | Inserts - Crimp Contact   |
| Insert Series  | S-M40/3C  |
| Product Name   | Heavy-Duty Connectors   |
| Standard       | CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977  |
| UPC            | 887191829029  |

### **Agency**

|    |         |
|----|---------|
| UL | E249674 |
|----|---------|

### **Electrical**

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 40.0A |
| Voltage - Maximum             | 500V  |

### **Physical**

|                                |               |
|--------------------------------|---------------|
| Component Size                 | «34.2x14.6»   |
| Durability (mating cycles max) | 500           |
| Gender                         | Male          |
| Insert Color                   | Grey          |
| Material - Insert              | Polycarbonate |
| Net Weight                     | 13.700/g      |
| Number of Rows                 | 1             |
| Packaging Type                 | Bag           |
| Polarized to Mating Part       | Yes           |

---

|                               |                |
|-------------------------------|----------------|
| Poles                         | 3              |
| Temperature Range - Operating | -40° to +125°C |

---

## Mates With / Use With

### Mates with Part(s)

| Description   | Part Number      |
|---|------------------|
| Heavy-Duty Crimp Contact Insert,<br>Female, 3-Pole, 40A, for Crimp<br>Contacts, Size «34.2x14.60» | <u>936010525</u> |

### Use with Part(s)

| Description | Part Number            |
|-------------|------------------------|
| Use With    | Turned Contacts - Male |

---

This document was generated on Sep 23, 2025