






P	LTR	DESCRIPTION	DATE	DWN	AP
	A1	REVISED PER ECR-17-015449	25OCT2017	BDA	KR
	A2	REVISED PER ECO-20-008510	17JUN2020	WLS	DZ
	A3	REVISED PER ECN-20-100768	03DEC2020	WLS	VS
	B	REVISED PER ECN-21-103649	10MAY2021	WLS	VS



RECOMMENDED
PANEL CUT-OUT

SCALE 2:1



- ① LOCKNUT : METAL
HOUSING : NYLON, FLAME RETARDANT, UL94-VO
O-RING : NEOPRENE BLACK (-I) OR
SILICONE RUBBER RED (I- -I).
- ② LOCKNUT : PLATED
- ③ LOCKNUT, SIX(6) OR EIGHT(8) SYMETRICAL
PLACED GRIP POINTS PERMISSIBLE.
- 4 DIMENSIONS SHOWN REPRESENT PRODUCT
IN DRY, AS MOLDED, CONDITION.
ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT
MOISTURE ABSORPTION MAY OCCUR AND
SHOULD BE ACCOUNTED FOR.
- ⑤ ROHS COMPLIANT.

OBSOLETE	5	1-1604256-
		1604256
		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22APR2002 J.C. YOSIER CHK 22APR2002 J.H. WEAVER APVD 22APR2002 J.H. WEAVER		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME BULKHEAD CONNECTOR ASSEMBLY 4 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)	
		0 PLC ±.01 1 PLC ±0.5 [.021] 2 PLC ±0.13 [1.005] 3 PLC ±. 4 PLC ±. ANGLES ±.			
MATERIAL		WEIGHT -			
				SIZE CAGE CODE DRAWING NO RESTRICTED A200779 C-1604256	
CUSTOMER DRAWING				SCALE 3:1	SHEET OF REV