



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B9	REVISED PER ECR-19-005348	09APR2019	WH	DZ



0	X	0	0	0	X	0						7	NATURAL	27.72	1-1744525-7
0	0	0	0	0	X	0	X	0				9	NATURAL	35.64	3-1744525-9
0	0	X	0	0	X	0	X	0				9	NATURAL	35.64	2-1744525-9
0	0	0	X	0	X	0						7	NATURAL	27.72	1744525-7
X	0	X	0	X	0	X	0	X				9	NATURAL	35.64	1-1744525-9
X	0											2	NATURAL	7.92	1744525-2
0	0	0	0	0	0	0	0	0	X	0		11	NATURAL	43.56	1-1744525-1
0	X	0	X	0	X	0	X	0				9	NATURAL	35.64	1744525-9
0	X	0	0	0	0							6	NATURAL	23.76	2-1744525-6
0	X	0	X	0								5	NATURAL	19.80	2-1744525-5
0	X	0	0									4	NATURAL	15.84	2-1744525-4
0	X	0	0	0	X	0	0	0	0	0	0	12	NATURAL	47.52	1-1744525-2
0	0	X	0	0								5	NATURAL	19.80	1744525-5
0	0	X	0									4	NATURAL	15.84	1744525-4
0	X	0										3	NATURAL	11.88	1744525-3
1	2	3	4	5	6	7	8	9	10	11	12	NO. OF POSITIONS	COLOR	DIM A ±0.30	PART NUMBER
PIN POSITIONS											5				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 22MAR13		TE Connectivity							
		CHK TOM MICHELUTTI 22MAR13									
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, EP HEADER, RIGHT ANGLE							
mm											
		0 PLC ± 0.3									
		1 PLC ± 0.25									
		2 PLC ± 0.13									
		3 PLC ± 0.05									
4 PLC ± 0.05		APVD TOM MICHELUTTI 22MAR13		SIZE A2							
ANGLES ± 3.0°		PRODUCT SPEC 108-5609									
		APPLICATION SPEC 114-5253									
MATERIAL -		FINISH -		WEIGHT -		CAGE CODE 00779		DRAWING NO C-1744525		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE N/A		SHEET 1 OF 1		REV B9			