




PART NO	DRAWING NO	CABLE LENGTH "L"	COLOR
912M-2-1-00100	671-444-A	1000±100	Orange
912M-2-1-00200	671-444-B	2000±100	Orange
912M-2-1-00300	671-444-C	3000±100	Orange
912M-2-1-00500	671-444-D	5000±100	Orange
912M-2-1-00700	671-444-E	7000±100	Orange
912M-2-1-01000	671-444-F	10000±100	Orange
912M-2-1-01500	671-444-G	15000±100	Orange
912M-2-1-02000	671-444-H	20000±100	Orange
912M-2-1-02500	671-444-I	25000±100	Orange

NOTES:
Insertion loss < 0.3 dB

6	Dust Cover
5	$\frac{1}{2}$ Code
4	Shrinkage Tube
3	SC MM Duplex Connector (Beige housing Red/black boot)
2	LC MM Duplex Connector (Beige housing White boot)
1	2.0mm,Duplex,MM-62.5/125 OM1, PVC, Optical Fiber Cable(Orange)
No.	Description

CnC Tech, LLC Industrial Cable and Connector Technology					
		TITLE	Patch Cord, LC-SC,MM-62.5/125 OM1, Duplex, PVC, orange, 2.0mm, xxm		
UNIT	mm	P/N	above	DRAWN BY	
unless otherwise stated Tolerances mm angular XXX.XX ±0.3 ±2° XX.XX ±0.2 X.XX ±0.1		Customer P/N	912M-2-1-0XXXX	CHECK BY	
		SIZE A4	SCALE Free	PAGE 1/1	APPROVAL BY

CHECK BY