

4-Port USB-C Hub, USB C to 2x USB-A, 2x USB-C, USB 3.0, Black

MODEL NUMBER: **U460-004-2A2CB**



Adds 2 USB-A and 2 USB-C ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U460-004-2A2CB 4-Port USB 3.1 Gen 1 USB-C Portable Hub expands the potential of your tablet, laptop, MacBook, Chromebook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals and charging a mobile device—all at the same time. The plug-and-play U460-004-2A2CB requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time. Dual USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and provide up to 0.9A each for charging smartphones and other mobile devices. They support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. Dual USB-C ports also connect to a wide range of USB devices, including external hard drives and tablets. Each provides up to 1.5A of charging power. They also support USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations.

Features

Turn Your Device's USB-C Port into a Multiport Workstation Ideal for adding USB peripherals and charging mobile devices simultaneously
 Plug-and-play operation with no software, drivers or external power required
 About the size of a credit card for easy carrying in a pocket, purse or laptop bag

Connect USB Peripherals 2 USB-A ports provide up to 0.9A each for charging devices
 2 USB-C ports provide up to 1.5A each for charging devices
 Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
 Backward compatible with USB 2.0 and USB 1.1

Note: Host must support USB OTG (On-the-Go)

Built-In Cable with Reversible USB-C Connector Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Specifications

Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- USB-C ports provide up to 1.5A each for charging devices
- USB-A ports provide up to 0.9A each for charging devices
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port (USB 3.1 port needed to achieve USB 3.1 speeds)

Package Includes

- U460-004-2A2CB USB 3.1 Gen 1 USB-C Portable Hub, Black
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332209207
Product Type	Hub
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(2) USB A (FEMALE); (2) USB C (FEMALE)
Data Ports Details	(2) USB-A - USB 3.2 Gen 1 (5 Gbps); (2) USB-C - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Consumption (Watts)	2.5
CHARGING	
Charging Ports / Amps	(2) 0.9A; (2) 1.5A
PHYSICAL	
Material of Construction	Plastic
Color	Black
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	0.80 x 3.80 x 4.70
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / in.)	0.55 x 3 x 1.7



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Packaging Type	Box
Unit Weight (lbs.)	0.07
Unit Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	8.5 BTU/Hr
Power Provided to Connected Device(s)	USB-A Port: 900mA; USB-C: 1.5A
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(2) USB 3.0 A (FEMALE)
Side B - Connector 2	(2) USB C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, IC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>