

# MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY

FREDPORT, ILLINOIS

FED. MFR. CODE 91929

## SWITCH - BASIC

CATALOG LISTING  
BZ - RW822

CATALOG LISTING  
BZ - RW822

ISSUE  
12

### REVISIONS

|   |                                     |
|---|-------------------------------------|
| A | CO<br>16736<br>G C H<br>30 MAR 62   |
| B | CO23645<br>M B F<br>23 JAN 68       |
| C | CO46304<br>J A P<br>12 OCT 79       |
| D | CO<br>58037<br>SMA<br>1 OCT 85      |
| E | CO<br>70184-H<br>G R T<br>2 JUN 92  |
| F | CO-<br>75204B<br>DAW<br>1 FEB 94    |
| G | CO-<br>78874<br>DLT<br>18 NOV 94    |
| H | CO-<br>94212-J<br>J J A<br>5 OCT 99 |
| J | 203155<br>CSL<br>24 MAY 01          |

REPLACES

RELEASE NO.

CHECK

CHECK

11 APR 62

DAW


CHECK

30 MAR 62

RASTER

FO-30378

DRAWN



NOTE  
MOUNTING HOLES WILL ACCEPT PINS OR SCREWS  
OF .139 MAX DIA ON 1.000 ± .002 CENTERS.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

### CHARACTERISTICS

OPERATING FORCE ----- 5 1/2 OZ MAX  
RELEASE FORCE ----- 1 1/2 OZ MIN  
DIFFERENTIAL TRAVEL ----- .001 - .006  
OVERTRAVEL ----- .094 MIN

### ELECTRICAL DATA

#### CONTACT ARRANGEMENT

S P D T

L103 15A 125, 250 OR 480 VAC  
1/8HP 125 VAC, 1/4HP 250 VAC

L288  
L299  
L306



16A 250V ~ T85 5E4

### SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE  
SPECIFIED  
DIMENSIONS ARE IN INCHES  
TOLERANCES ARE:

ONE PLACE (.0) ± .030  
TWO PLACE (.00) ± .015  
THREE PLACE (.000) ± .005  
ANGLES ±

WEIGHT .063 LB