


used for: DIN 41651



PCB-HOLE DRILLINGS





NOTES:

1. PLASTIC HOUSING SPECIFICATION
   - PLASTIC MATERIAL: PBT 20% GF
   - PRODUCT RATING: UL-94 V-0
2. CONTACT SPECIFICATION
   - CONTACT: COPPER ALLOY
   - PLATING: GOLD PLATED; 50 MATING CYCLES
3. PERFORMANCE RATING
   - WITHSTANDING VOLTAGE: 1000 V DC or AC PEAK
   - CURRENT RATING: 1.0 A
   - CONTACT RESISTANCE: 20 mOhm
   - INSULATION RESISTANCE: 5000 MOhm at 100 V
   - NORMAL OPERATING TEMPERATURE:
     -40 DEGREE TO +105 DEGREE CENTIGRADE

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Original		

tolerance

	date	name
2016		
drawn	05.07.	Lehmenkühler
appd.	05.07.	Henneboel
norm	DIN 41651	
d-old		

scale: 2:1
material: SEE NOTES

title:
LOW PROFILE HEADER
10pos.
with straight solder pins 4,5mm

dwg no: 14K1A036 | AutoCAD | DIN-A 4 | sh: 1/1

part no: 141A11729X

Downloaded from Arrow.com.