


MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929**SWITCH — BASIC**


CATALOG LISTING

BZ-RW8435161-A2**NOTES:**

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE — 7 GRAMS MAX

DIFFERENTIAL TRAVEL — .003 — .012

OVERTRAVEL — .203 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

S P D T

L95

10A 125, 250 OR 480 VAC
1/8HP 125 VAC, 1/4HP 250 VAC

L288



SCALE

FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 2

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/64	X	0.01/0.25
ONE PLACE	X.X	0.01/0.10	X.X	0.01/0.10
TWO PLACES	X.XX	0.001/0.005	X.XX	0.001/0.015
THREE PLACES	X.XXX	0.0001/0.0005	X.XXX	0.0001/0.0005
ANGLES				

DESIGN UNITS

SI METRIC

US CUSTOMARY

WEIGHT .073 LB

CATALOG LISTING

BZ-RW8435161-A2

PAGE 1 OF 1

MISSUE
5

REVISIONS

A	C064626	YJA	16 JUN 89
B	CO-73287-J	JAL	22 NOV 93
C	CO-77589	MAM	29 MAR 94
D	203222	CSL	6 JUN 01

CHECK

CHECK

RASTER

0-52848-A

DRAWN

CHECK

A P 124 SEPT 88

REPLACES X89225-BZ

RELEASE NO. RR-16777

MICRO SWITCHFREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929**SWITCH — BASIC**

CATALOG LISTING

BZ-RW8435161-A2**M BZ-RW8435161-A2**

REPLACES X89225-BZ

RELEASE NO. PR-16777

DRAWING
NUMBER

X8

ISSUE

X4

CHECK

REVISIONS

A C064626

YJA

16 JUN 89

B CO-

73287-J

JAL

22 NOV 93


C CO-

77589

MAM

29 MAR 94

CHECK




NOTES:

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE — 7 GRAMS MAX

DIFFERENTIAL TRAVEL — .003 — .012

OVERTRAVEL — .203 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

S P D T

L95
10A 125, 250 OR 480 VAC
1/8 HP 125 VAC, 1/4 HP 250 VAC



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. in	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04	X	0.07/0.03
ONE PLACE	X, X	0.47/.010	X, X	0.38/.015
TWO PLACES	X, X, X	0.10/.005	X, X, X	0.13/.005
THREE PLACES				
ANGLES				

DESIGN UNITS ☐ SI METRICUS CUSTOMARY ☐

WEIGHT .073 LB

O-52848-A

DRAWN

CHECK

J A P 24 SEPT 88