THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED(ECR-13-012673)	05.SEP.'13	CJ	HG
	A2	REVISED(ECR-20-011452)	13.AUG.'20	JH	GC







TABLE 1. APPLICABLE REC. CONTACT.


REC.	PART NO.	WIRE RANGE(mm^2)	INSULATION DIA.(mm) (FLR)
MQS (0.64)	1355717	0.14-0.22	0.9-1.2
	928999	0.2-0.5	0.9-1.6
	963715	0.5-0.75	1.6-1.9
MCP 2.8	A2 1564982	0.2-0.35	1.1-1.4
	1241388	0.5-1.0	1.4-2.1
	1241390	1.0-2.5	2.2-3.0
	968853	2.5-4.0	3.0-3.7



ISO VIEW







NOTE ;

1. GENERAL TOLERANCE : ±0.3, ±3.0°
2. APPLICABLE REC. CONTACT : SEE TABLE 1.
3. THE MATING CAP ASS'Y P/N : 1897540
4. DELIVERY CONDITION : TPA 1'ST LOCKING.
5. CURCUIT NO.
6. MATERIAL ID MARK
   - 1897543-2 : >PBT-GF15<
   - 1897543-1 : >PA66-GF10<
7. APPLICATION
   - 1897543-2 : FOR IN-LINE CONNECTOR
   - 1897543-1 : FOR TRANSMISSION CONNECTOR

NO.	PART NO.	DESCRIPTION	MATERIAL	COLOR	Q'TY	
2	1897545-6	PLUG DBL	PA66-GF10	RED	1	
	1897545-1		PBT	WHITE		1
1	1897544-1	PLUG HSG	PA66-GF10	NATURAL	1	
	1897544-2		PBT-GF15	BLACK		1

ASS'Y P/N	DESCRIPTION	REMARK
1897543-1	PLUG HSG ASS'Y	
1897543-2	PLUG HSG ASS'Y	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±-

MATERIAL - -

FINISH - -

DWN CJ CHOI -
CHK KT LIM -
APVD HG CHO -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME - HYB(MQS/MCP2.8)22P PLUG HSG ASS'Y -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1897543	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV A2

1470-19 (3/13)

Downloaded from Arrow.com.