

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301080162

Status:

Active

Overview:

Wide-Area Lighting Products

Description:

Super-Safeway Twin Tube 64W Fluorescent Work Light with 16/3 SJOW 7.62m (25.0') Cord Length



Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E174254
General	
Product Family	Portable Lighting
Series	130108
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Wide-Area Lighting Products
Product Name	Super-Safeway
Taxonomy	Lamps and Lights
Type	Wide Area Lamps
UPC	78678867148
Physical	
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	190.75mm (7.510")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	82.55mm (3.250")
Length	1.39m (54.620")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Adjustable Brackets
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Fluorescent
Cord Type - Primary	16/3 SJOW
Lamp Type	F32/T8
Lamp Wattage - Maximum	64W
Lumens	5700
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	1350

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130108 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION