



Part Number : [1300990110](#)
Product Description : MAX-LOC Strain Relief Cord-
Sealing Grip, 1" NPT, Straight Male, Cable Diameter
11.10-14.27mm (.437-.562"), Stainless Steel Mesh
Series Number : 130099
Status : Active
Product Category : Cable Grips
Engineering Number : 5546M



Documents & Resources

Drawings
[1300990110 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130099
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, Straight Male, Cable Diameter 11.10-14.27mm (.437-.562"), Stainless Steel Mesh
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678855464

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	11.10-14.27mm (.437-.562")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	Stainless Steel
Mesh Length	N/A
Number of Holes	1
O-Ring	No
Thread Size	1" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1" NPT	<u>1300990145</u>
MAX-LOC Gasket Sealing Ring, 1" NPT, Black	<u>1300990151</u>
MAX-LOC O-Ring, 1" NPT	<u>1301800334</u>

This document was generated on Sep 25, 2025